



# PURON<sup>®</sup> MP Hollow Fiber Cartridge

8-inch Ultrafiltration Cartridge for Water and Wastewater Filtration

## PRODUCT DESCRIPTION

<b>Membrane Chemistry:</b>	Proprietary PVDF
<b>Membrane Type:</b>	Braided hollow fiber for outside-in operation
<b>Fiber Support Chemistry:</b>	Polyester
<b>Nominal Pore Size:</b>	0.03 µm
<b>Outside Fiber Diameter:</b>	0.1 inch (2.6 mm)
<b>Housing Shell:</b>	PVC
<b>Potting Material:</b>	Proprietary Epoxy Compound
<b>Storage Solution:</b>	Glycerin/Water
<b>Regulatory Status:</b>	Classified by UL to NSF/ANSI Standard 61 and in accordance with NSF/ANSI Standard 372. Part number 0728000-LT2 meets State of California LT2 test requirements.

## PRODUCT SPECIFICATIONS

Part Number	Model	Membrane Area [ft <sup>2</sup> (m <sup>2</sup> )]	Typical Production Range [gpm (m <sup>3</sup> /hr)]
0728000	PURON <sup>®</sup> MP 8081-102	546 (51)	9 - 30 (2 - 6.8)
0728000-LT2	PURON <sup>®</sup> MP 8081-102	546 (51)	9 - 30 (2 - 6.8)


## OPERATING AND DESIGN INFORMATION\*

<b>Maximum Pressure (water):</b>	45 psi (3.0 bar)** @ 104° F (40° C) or less
<b>Temperature Range:</b>	32° F (0° C) - 104° F (40° C)
<b>Maximum Production Transmembrane Pressure:</b>	25 psi (1.7 bar)
<b>Maximum Backflush Transmembrane Pressure:</b>	10 psi (0.7 bar)
<b>Allowable pH Range (continuous operation):</b>	4 - 9
<b>Allowable pH Range (short term):</b>	1.8 - 10.5
<b>Maximum Total Chlorine @ 77° F (25° C) or lower:</b>	1,000 ppm @ pH <10.5
<b>Typical Air Scour Rate per Cartridge:</b>	7 scfm (12 Nm <sup>3</sup> /hr)
<b>Maximum Air Scour Rate per Cartridge:</b>	9 scfm (15 Nm <sup>3</sup> /hr)
<b>Typical Backflush Flow Rate per Cartridge:</b>	19 gpm (4.3 m <sup>3</sup> /hr)

\*Consult KSS Process Engineering Group for specific applications

\*\*Higher pressure, up to 3.6 bar (52 psi) requires specific approval of KSS Process Engineering group

## NOMINAL DIMENSIONS



Model	D		L1		L2		L3	
	inches	(mm)	inches	(mm)	inches	(mm)	inches	(mm)
PURON <sup>®</sup> MP 8081-102	8.6	(220)	81	(2,060)	84 <sup>9</sup> / <sub>16</sub>	(2,148)	91 <sup>9</sup> / <sub>16</sub>	(2,326)

\* Dimensions are provided for reference only and should not be interpreted as accurate specifications.

Note: Generation II Design shown



**STORAGE GUIDELINES**

**Cartridge Storage Conditions:**

New cartridges are packaged in a glycerin/water solution. The glycerin/water solution should be removed from new cartridges before their initial use with a water rinse followed by a chlorine clean. See the pre-startup cleaning instruction sheet packed with each cartridge shipment for more details. Prior to installation, cartridges should be stored in their original packaging under the following conditions:

- Indoors, out of direct sunlight.
- Temperatures between 50 - 85°F (10 - 30°C).
- Relative humidity below 70%.
- In a horizontal position (unless shipped as fully loaded crate).

It is best to use new cartridges within one year of shipment. Consult KSS for recommendations for longer term storage.

Used cartridges should be cleaned, rinsed and impregnated before storage using a solution of 80-100% glycerin. New cartridge storage conditions should also be used for used cartridges. Used cartridges must be drained, rinsed, and cleaned after storage per the pre-startup cleaning instruction sheet.

**CARTRIDGE ASSEMBLY AND COMPONENTS**

Item	Description	Quantity Required
1	Vent End Cap	1 each
2	Aeration End Cap	1 each
3	Face Seal	2 each
4	V-Band coupling	2 each
5	O-rings	2 each
6	PURON® MP Cartridge	1 each

Note: Generation II End Cap Design shown

**Generation II PURON® MP Pass Kit**

(includes items 1-5 on right)

Standard part number 1021079

**Generation I PURON® MP Pass Kit**

Part Number: 1021034

**PURON® MP Seal Kit**

(Includes 2 each of items 3 & 5 for both GENERATION I and II designs)

Part Number: 1021082

**PURON® MP Pinning Kits**

Standard part number 1021076

Silicone free part number KDP3729

**Process Connections:**

Feed, Permeate and Vent ports: 1½" Groove end couplings

Air Scouring connection: ½" OD tubing


O-Rings: Parker 2-221 EPDM

**Cartridge Weight and Hold Up Volume:**

Cartridge shipping weight: 98 lbs (44.5 kg)

Cartridge hardware (Pass kit) weight: 12 lbs (5.5 kg)

Hold up volume: 10 gallons (38 Liters)



NOTE: GEN II END CAP DESIGN SHOWN

*The information contained in this publication is believed to be accurate and reliable, but is not to be construed as implying any warranty or guarantee of performance. We assume no responsibility, obligation or liability for results obtained or damages incurred through the application of the information contained herein. Refer to Standard Terms and Conditions of Sale and Performance Warranty documentation for additional information*

**Koch Separation Solutions, Inc.** 850 Main Street, Wilmington, MA 01887  
 Main: +1-978-694-7000 • Fax: +1-978-657-5208 • Toll Free: +1-888-677-5624

For complete contact information and listing of our global locations, visit [www.kochseparation.com](http://www.kochseparation.com)

©2020 Koch Separation Solutions, Inc. All rights reserved worldwide. For related trademark information, visit [www.kochseparation.com/legal](http://www.kochseparation.com/legal).